

EXTEC Diamond Grinding Discs are available in standard sizes in both metal or resin bonded varieties with Pressure Sensitive Adhesive (PSA), plain back or overhanging cloth. They are recommended for coarse and fine grinding of high hardness materials. Metal flex feature a flexible, color-coded, open patterned metal bonded disc for aggressive cutting and reduced loading.

Resin flex feature a flexible, color-coded, open patterned resin bonded disc for aggressive cutting. Metal bonded discs consist of a high quality diamond abrasive grit bonded to a wheel by an electroplating process. Resin bonded discs also consist of a high quality diamond abrasive grit bonded to a flat aluminum disc with resin.



CATALOG NUMBER	DESCRIPTION	UNIT
EXTEC Diamond Metal Flex Disc 8" (203 mm) PSA		
16120	250 µm Green	Each
16122	125 µm Black	Each
16124	74 µm Red	Each
16126	40 µm Yellow	Each
16128	20 µm White	Each
16129	10 µm Blue	Each
EXTEC Diamond Metal Flex Disc 250 mm PSA		
16088	250 µm Green	Each
16090	125 µm Black	Each
16092	74 µm Red	Each
16094	40 µm Yellow	Each
16096	20 µm White	Each
16098	10 µm Blue	Each
EXTEC Diamond Metal Flex Disc 12" (305 mm) PSA		
16108	250 µm Green	Each
16110	125 µm Black	Each
16112	74 µm Red	Each
16114	40 µm Yellow	Each
16116	20 µm White	Each
16118	10 µm Blue	Each
EXTEC Diamond Resin Flex Disc 8" (203 mm) PSA		
20977	30 µm Yellow	Each
20978	10 µm Blue	Each
20979	2 µm Orange	Each
EXTEC Diamond Resin Flex Disc 250 mm PSA		
20976	30 µm Yellow	Each
20983	10 µm Blue	Each
20984	2 µm Orange	Each
EXTEC Diamond Resin Flex Disc 12" (305 mm) PSA		
20980	30 µm Yellow	Each
20981	10 µm Blue	Each
20982	2 µm Orange	Each

DIAMOND DISCS

CATALOG NUMBER	DESCRIPTION	UNIT
EXTEC Diamond Disc Metal Bonded 2 7/8" (73 mm)		
20970	45 µm	Each
20972	30 µm	Each
20971	15 µm	Each
20975	6 µm	Each
EXTEC Diamond Disc Metal Bonded 8" (203 mm) PSA		
16302	165 µm	Each
16306	70 µm	Each
16312	45 µm	Each
16316	30 µm	Each
16322	15 µm	Each
16321	9 µm	Each
16319	6 µm	Each
EXTEC Diamond Disc Metal Bonded 8" (203 mm) Overhanging Cloth Back		
16301	165 µm	Each
16305	70 µm	Each
16311	45 µm	Each
16315	30 µm	Each
16320	15 µm	Each
16318	9 µm	Each
16317	6 µm	Each
EXTEC Diamond Disc Metal Bonded 250 mm PSA		
16323	165 µm	Each
16324	70 µm	Each
16325	45 µm	Each
16326	30 µm	Each
16327	15 µm	Each
16328	9 µm	Each
16329	6 µm	Each

CATALOG NUMBER	DESCRIPTION	UNIT
EXTEC Diamond Disc Metal Bonded 12" (305 mm) PSA		
16330	165 µm	Each
16331	70 µm	Each
16332	45 µm	Each
16333	30 µm	Each
16334	15 µm	Each
16335	9 µm	Each
16336	6 µm	Each

CATALOG NUMBER	DESCRIPTION	UNIT
EXTEC Diamond Disc Resin Bonded 8" (203 mm) PSA		
16232	300 µm	Each
16236	165 µm	Each
16242	70 µm	Each
16246	45 µm	Each
16252	30 µm	Each
16256	15 µm	Each
16262	9 µm	Each
16266	6 µm	Each
EXTEC Diamond Disc Resin Bonded 8" (203 mm) Overhanging Cloth Back		
16230	300 µm	Each
16235	150 µm	Each
16240	60 µm	Each
16245	45 µm	Each
16250	30 µm	Each
16255	15 µm	Each
16260	9 µm	Each
16265	6 µm	Each