

EXTEC Dia-lap CONTINUOUS Diamond Lapping Film Discs are recommended for carbides, ceramics, fiber optics, wafers, microelectronic devices, in addition to petrographic and high hardness metals where critical surface flatness is required.

Premium graded continuous diamond particles are resin bonded to highly uniform polyester film resulting in consistent performance for ultimate flatness and finish.

Dia-lap CONTINUOUS Diamond Lapping Film Discs are available for wet or dry (W/D) applications with Pressure Sensitive Adhesive (PSA) or Plain Back from 0.1 micron to 45 micron. Special size orders are also available.

EXTEC I Dia-lap INTERRUPTED Diamond Lapping Film Discs or Sheets have a longer life and are recommended for less critical applications requiring more aggressive materials removal. Available in discs and sheets from 0.5 micron to 9 micron. Special size orders are also available.

CATALOG NUMBER	DESCRIPTION	UNIT
EXTEC Dia-lap Diamond Lapping Film Disc W/D PolyBack 8" (203 mm) 3 mil Thickness		
15400	0.1 µm Gray Green	Pkg/5
15401	0.5 µm Off White	Pkg/5
15402	1 µm Lavender	Pkg/5
15403	3 µm Pink	Pkg/5
15404	6 µm Brown	Pkg/5
15405	9 µm Blue	Pkg/5
15406	15 µm Orange	Pkg/5
15407	30 µm Green	Pkg/5
15408	45 µm Amber	Pkg/5
EXTEC Dia-lap Diamond Lapping Film Disc W/D PolyBack PSA 8" (203 mm) 3 mil Thickness		
15409	0.1 µm Gray Green	Pkg/5
15410	0.5 µm Off White	Pkg/5
15411	1 µm Lavender	Pkg/5
15412	3 µm Pink	Pkg/5
15413	6 µm Brown	Pkg/5
15414	9 µm Blue	Pkg/5
15415	15 µm Orange	Pkg/5
15416	30 µm Green	Pkg/5
15417	45 µm Amber	Pkg/5
EXTEC Dia-lap Diamond Lapping Film Disc W/D PolyBack 12" (305 mm) 3 mil Thickness		
15420	0.1 µm Gray Green	Pkg/3
15421	0.5 µm Off White	Pkg/3
15422	1 µm Lavender	Pkg/3
15423	3 µm Pink	Pkg/3
15424	6 µm Brown	Pkg/3
15425	9 µm Blue	Pkg/3
15426	15 µm Orange	Pkg/3
15427	30 µm Green	Pkg/3
15428	45 µm Amber	Pkg/3
EXTEC Dia-lap Diamond Lapping Film Disc W/D PolyBack PSA 12" (305 mm) 3 mil Thickness		
15429	0.1 µm Gray Green	Pkg/3
15430	0.5 µm Off White	Pkg/3
15431	1 µm Lavender	Pkg/3
15432	3 µm Pink	Pkg/3
15433	6 µm Brown	Pkg/3
15434	9 µm Blue	Pkg/3
15435	15 µm Orange	Pkg/3
15436	30 µm Green	Pkg/3
15437	45 µm Amber	Pkg/3

CATALOG NUMBER	DESCRIPTION	UNIT
EXTEC I Dia-lap INTERRUPTED Diamond Lapping Film Disc W/D Plain Backed 8" (203 mm)		
15468	0.5 µm Off White	Pkg/5
15469	1 µm Lavender	Pkg/5
15470	3 µm Pink	Pkg/5
15471	6 µm Brown	Pkg/5
15472	9 µm Blue	Pkg/5
EXTEC I Dia-lap INTERRUPTED Diamond Lapping Film Disc W/D PSA 8" (203 mm)		
15459	0.5 µm Off White	Pkg/5
15460	1 µm Lavender	Pkg/5
15461	3 µm Pink	Pkg/5
15462	6 µm Brown	Pkg/5
15463	9 µm Blue	Pkg/5
EXTEC I Dia-lap INTERRUPTED Diamond Lapping Film Disc W/D Plain Backed 12" (305 mm)		
15486	0.5 µm Off White	Pkg/3
15487	1 µm Lavender	Pkg/3
15488	3 µm Pink	Pkg/3
15489	6 µm Brown	Pkg/3
15490	9 µm Blue	Pkg/3
EXTEC I Dia-lap INTERRUPTED Diamond Lapping Film Disc W/D PSA 12" (305 mm)		
15477	0.5 µm Off White	Pkg/3
15478	1 µm Lavender	Pkg/3
15479	3 µm Pink	Pkg/3
15480	6 µm Brown	Pkg/3
15481	9 µm Blue	Pkg/3
EXTEC I Dia-lap INTERRUPTED Diamond Lapping Film Sheet W/D Plain Backed 6" x 6" (152 mm x 152 mm)		
15491	0.5 µm Off White	Pkg/3
15492	1 µm Lavender	Pkg/3
15493	3 µm Pink	Pkg/3
15494	6 µm Brown	Pkg/3
15495	9 µm Blue	Pkg/3

